



RJ45 Patch Cord, category 5e, PVC stranded, with security key, gray, 3 m

Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA

Dimensions

Cord Length	3.00 m 9.84 ft
Diameter Over Jacket	4.90 mm 0.19 in

Electrical Specifications

ANSI/TIA Category	5e
--------------------------	----

Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	CM
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug with security key
Interface, connector B	RJ45 plug with security key
Jacket Color	Gray
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Stranded
Conductor Gauge, stranded	24 AWG
Conductor Material	Bare copper

Regulatory Compliance/Certifications

Agency

Classification

