

RJ45 Consolidation Point Cable, UTP, white, 15 m

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair patch cord
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA

## Dimensions

<b>Cord Length</b>	15.00 m   49.21 ft
<b>Diameter Over Jacket</b>	5.59 mm   0.22 in

## Electrical Specifications

<b>ANSI/TIA Category</b>	6
--------------------------	---

## Environmental Specifications

<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)

## General Specifications

<b>Cable Type</b>	U/UTP (unshielded)
<b>Interface, connector A</b>	RJ45 plug
<b>Interface, connector B</b>	RJ45 jack
<b>Jacket Color</b>	White
<b>Pairs, quantity</b>	4

## Regulatory Compliance/Certifications

<b>Agency</b>	RoHS 2011/65/EU
---------------	-----------------

<b>Classification</b>	Compliant
-----------------------	-----------

