

RJ45 Consolidation Point Cable, UTP, white, 10 m

Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA

Dimensions

Cord Length	10.00 m 32.81 ft
Diameter Over Jacket	5.59 mm 0.22 in

Electrical Specifications

ANSI/TIA Category	6
--------------------------	---

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 jack
Jacket Color	White
Pairs, quantity	4

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

