

RJ45 Consolidation Point Cable, plug to jack, S/FTP, white, 10 m



Product Classification

| | |
|------------------------------|-------------------------------------|
| Portfolio | NETCONNECT® |
| Product Type | Twisted pair patch cord |
| Regional Availability | Asia Australia/New Zealand EMEA |

Dimensions

| | |
|-----------------------------|--------------------|
| Cord Length | 10.00 m 32.81 ft |
| Diameter Over Jacket | 5.59 mm 0.22 in |

Electrical Specifications

| | |
|--------------------------|----|
| ANSI/TIA Category | 6A |
|--------------------------|----|

Environmental Specifications

| | |
|------------------------------|-------------------------------------|
| Environmental Space | Low Smoke Zero Halogen (LSZH) |
| Operating Temperature | -20 °C to +60 °C (-4 °F to +140 °F) |

General Specifications

| | |
|-------------------------------|------------------|
| Cable Type | S/FTP (shielded) |
| Interface, connector A | RJ45 plug |
| Interface, connector B | RJ45 jack |
| Jacket Color | White |
| Pairs, quantity | 4 |

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

