



MPO Trunk Cable, 24F, MPO male, OM4, LSZH, flipped, 15 m, aqua

Product Classification

Portfolio	NETCONNECT®
Brand	MPOptimate®
Product Type	Fiber trunk cable assembly
Regional Availability	Asia

Construction Materials

Fiber Type	OM4
Total Fibers, quantity	24
Jacket Color	Aqua
Fiber Mode	Multimode

Dimensions

Cord Length	15.00 m 49.21 ft
Diameter Over Jacket	7.50 mm 0.30 in

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

General Specifications

Interface, connector A	MPO-12/UPC Male
Interface, connector B	MPO-12/UPC Male
Color, connector A	Mustard
Color, connector B	Mustard
Color, boot A	Black
Color, boot B	Red
Connector A, quantity	2
Connector B, quantity	2
Package Quantity	1
Polarity	Pairs, flipped

Optical Performance

Insertion Loss, maximum, connector A 0.35 dB

Insertion Loss, maximum, connector B 0.35 dB

Return Loss, minimum, connector A 28.00 dB

Return Loss, minimum, connector B 28.00 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

