



MPO Trunk Cable, 24F, MPO male, OM4, LSZH, flipped, 14 m, aqua

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Brand</b>	MPOptimate®
<b>Product Type</b>	Fiber trunk cable assembly
<b>Regional Availability</b>	Asia

## Construction Materials

<b>Fiber Type</b>	OM4
<b>Total Fibers, quantity</b>	24
<b>Jacket Color</b>	Aqua
<b>Fiber Mode</b>	Multimode

## Dimensions

<b>Cord Length</b>	14.00 m   45.93 ft
<b>Diameter Over Jacket</b>	7.50 mm   0.30 in

## Environmental Specifications

<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

## General Specifications

<b>Interface, connector A</b>	MPO-12/UPC Male
<b>Interface, connector B</b>	MPO-12/UPC Male
<b>Color, connector A</b>	Mustard
<b>Color, connector B</b>	Mustard
<b>Color, boot A</b>	Black
<b>Color, boot B</b>	Red
<b>Connector A, quantity</b>	2
<b>Connector B, quantity</b>	2
<b>Package Quantity</b>	1
<b>Polarity</b>	Pairs, flipped

## Optical Performance

**Insertion Loss, maximum, connector A** 0.35 dB

**Insertion Loss, maximum, connector B** 0.35 dB

**Return Loss, minimum, connector A** 28.00 dB

**Return Loss, minimum, connector B** 28.00 dB

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

