



RJ45 Patch Cord, category 5e, PVC stranded, with security key, gray, 10 m

Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA

Dimensions

Cord Length	10.00 m 32.81 ft
--------------------	--------------------

Electrical Specifications

ANSI/TIA Category	5e
--------------------------	----

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
------------------------------	-------------------------------------

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug with security key
Interface, connector B	RJ45 plug with security key
Jacket Color	Gray
Interface Feature, connector A	Keyed
Interface Feature, connector B	Keyed
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Stranded
Conductor Gauge, stranded	24 AWG
Plug Insertion Life, minimum	750 times
Wiring	T568A

Regulatory Compliance/Certifications

Agency

Classification

