



MPO Trunk Cable, 2x12 fiber, OM3, MPO female-female, LSZH, straight, 11 m, aqua

## Product Classification

|                              |                              |
|------------------------------|------------------------------|
| <b>Portfolio</b>             | NETCONNECT®                  |
| <b>Brand</b>                 | MPOptimate®                  |
| <b>Product Type</b>          | Fiber trunk cable assembly   |
| <b>Regional Availability</b> | Australia/New Zealand   EMEA |

## Construction Materials

|                               |           |
|-------------------------------|-----------|
| <b>Fiber Type</b>             | OM3       |
| <b>Total Fibers, quantity</b> | 12        |
| <b>Jacket Color</b>           | Aqua      |
| <b>Fiber Mode</b>             | Multimode |

## Dimensions

|                             |                    |
|-----------------------------|--------------------|
| <b>Cord Length</b>          | 11.00 m   36.09 ft |
| <b>Diameter Over Jacket</b> | 8.00 mm   0.31 in  |

## Environmental Specifications

|                            |                               |
|----------------------------|-------------------------------|
| <b>Environmental Space</b> | Low Smoke Zero Halogen (LSZH) |
|----------------------------|-------------------------------|

## General Specifications

|                               |                   |
|-------------------------------|-------------------|
| <b>Interface, connector A</b> | MPO-12/UPC Female |
| <b>Interface, connector B</b> | MPO-12/UPC Female |
| <b>Color, connector A</b>     | Beige             |
| <b>Color, connector B</b>     | Beige             |
| <b>Color, boot A</b>          | Black             |
| <b>Color, boot B</b>          | Black             |
| <b>Connector A, quantity</b>  | 1                 |
| <b>Connector B, quantity</b>  | 1                 |
| <b>Package Quantity</b>       | 1                 |
| <b>Polarity</b>               | Pairs, straight   |

## Optical Performance

**Insertion Loss, maximum, connector A** 0.50 dB

**Insertion Loss, maximum, connector B** 0.50 dB

**Return Loss, minimum, connector A** 25.00 dB

**Return Loss, minimum, connector B** 25.00 dB

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant

