



MPO Trunk Cable, 12 fiber, singlemode, MPO female-female, LSZH, straight, 14 m, yellow

Product Classification

Portfolio	NETCONNECT®
Brand	MPOptimate®
Product Type	Fiber trunk cable assembly
Regional Availability	Australia/New Zealand EMEA

Construction Materials

Fiber Type	OS2
Total Fibers, quantity	12
Jacket Color	Yellow
Fiber Mode	Singlemode

Dimensions

Cord Length	14.00 m 45.93 ft
Diameter Over Jacket	6.40 mm 0.25 in

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

General Specifications

Interface, connector A	MPO-12/APC Female
Interface, connector B	MPO-12/APC Female
Color, connector A	Green
Color, connector B	Green
Color, boot A	Black
Color, boot B	Black
Connector A, quantity	1
Connector B, quantity	1
Package Quantity	1
Polarity	Pairs, straight

Optical Performance

Insertion Loss, maximum, connector A 0.60 dB

Insertion Loss, maximum, connector B 0.60 dB

Return Loss, minimum, connector A 45.00 dB

Return Loss, minimum, connector B 45.00 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

