

MPO Trunk Cable, 2x12 fiber, singlemode, MPO female-female, LSZH, straight, 17 m, yellow

Product Classification

Portfolio	NETCONNECT®
Brand	MPOptimate®
Product Type	Fiber trunk cable assembly
Regional Availability	Australia/New Zealand EMEA

Construction Materials

Fiber Type	OS2
Total Fibers, quantity	24
Jacket Color	Yellow
Fiber Mode	Singlemode

Dimensions

Cord Length	17.00 m 55.77 ft
Diameter Over Jacket	8.00 mm 0.31 in

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

General Specifications

Interface, connector A	MPO-12/APC Female
Interface, connector B	MPO-12/APC Female
Color, connector A	Green
Color, connector B	Green
Color, boot A	Black
Color, boot B	Black
Connector A, quantity	2
Connector B, quantity	2
Package Quantity	1
Polarity	Pairs, straight

Optical Performance

Insertion Loss, maximum, connector A	0.75 dB
Insertion Loss, maximum, connector B	0.75 dB
Return Loss, minimum, connector A	35.00 dB
Return Loss, minimum, connector B	35.00 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

