



MPOptimate® Trunk Cable, 24 fiber, duplex, OM4, 10 m, aqua

Product Classification

| | |
|------------------------------|------------------------------|
| Portfolio | NETCONNECT® |
| Brand | MPOptimate® |
| Product Type | Fiber trunk cable assembly |
| Regional Availability | Australia/New Zealand EMEA |

Construction Materials

| | |
|-------------------------------|-----------|
| Fiber Type | OM4 |
| Total Fibers, quantity | 24 |
| Jacket Color | Aqua |
| Fiber Mode | Multimode |

Dimensions

| | |
|-----------------------------|--------------------|
| Cord Length | 10.00 m 32.81 ft |
| Diameter Over Jacket | 8.00 mm 0.31 in |

Environmental Specifications

| | |
|----------------------------|-------------------------------|
| Environmental Space | Low Smoke Zero Halogen (LSZH) |
|----------------------------|-------------------------------|

General Specifications

| | |
|-------------------------------|-------------------|
| Interface, connector A | MPO-12/UPC Female |
| Interface, connector B | MPO-12/UPC Female |
| Color, connector A | Mustard |
| Color, connector B | Mustard |
| Color, boot A | Black |
| Color, boot B | Black |
| Connector A, quantity | 2 |
| Connector B, quantity | 2 |
| Package Quantity | 1 |
| Polarity | Pairs, straight |

Optical Performance

Insertion Loss, maximum, connector A 0.35 dB

Insertion Loss, maximum, connector B 0.35 dB

Return Loss, minimum, connector A 28.00 dB

Return Loss, minimum, connector B 28.00 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

