

MPO Trunk Cable, polarity A, 144 fiber (6x24) dual row, OFNP 3 mm, OS2, 10 m, with 36" breakouts

Product Classification

Portfolio	NETCONNECT®
Brand	MPOptimate®
Product Series	MPA
Product Type	Fiber trunk cable assembly
Regional Availability	Latin America North America

Construction Materials

Fiber Type	OS2
Total Fibers, quantity	144
Jacket Color	Yellow
Fiber Mode	Singlemode

Dimensions

Cord Length	10.00 m 32.81 ft
--------------------	--------------------

Environmental Specifications

Environmental Space	Plenum
----------------------------	--------

General Specifications

Interface, connector A	MPO-12/APC Female
Interface, connector B	MPO-12/APC Female
Color, connector A	Green
Color, connector B	Green
Color, boot A	Black
Color, boot B	Black
Connector A, quantity	6
Connector B, quantity	6
Package Quantity	1

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

