



MPOptimate® Trunk Cable, 48F, OM4, 10 m, aqua

Product Classification

Portfolio	NETCONNECT®
Brand	MPOptimate®
Product Type	Fiber trunk cable assembly
Regional Availability	EMEA

Construction Materials

Fiber Type	OM4
Total Fibers, quantity	48
Jacket Color	Aqua
Fiber Mode	Multimode

Dimensions

Breakout Length, connector A	700.02 mm 27.56 in
Breakout Length, connector B	700.02 mm 27.56 in
Cord Length	10.00 m 32.81 ft
Diameter Over Jacket	11.50 mm 0.45 in

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

General Specifications

Interface, connector A	MPO-12/UPC Female
Interface, connector B	MPO-12/UPC Female
Color, connector A	Aqua
Color, connector B	Beige
Color, boot A	Black
Color, boot B	Black
Connector A, quantity	4
Connector B, quantity	4
Package Quantity	1

1-2160075-0

Polarity

Pairs, straight

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

