

BK4V-STM



WECO Midsize Plug to Midsize Plug, 1.22 m, black

Product Classification

Product Type	RF cable assembly
Regional Availability	EMEA Latin America North America

Dimensions

Cord Length	1.22 m 4.00 ft
--------------------	------------------

Electrical Specifications

Data Rate, Supported	Uncompressed HDTV signals (1.485 Gbit/s)
Impedance	75 ohm
Safety Voltage Rating	600 V

Environmental Specifications

Environmental Space	Indoor
Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)

General Specifications

Cable Type	RG59, single
Interface, connector A	Midsize plug
Interface, connector B	Midsize plug
Jacket Color	Black
Application	For use with Midsize video panels
Interface Feature, connector A	Booted
Interface Feature, connector B	Booted

Mechanical Specifications

Conductor Gauge, stranded	22 AWG
Conductor Material	Beryllium copper
Contact Plating Material	Gold

Regulatory Compliance/Certifications

BK4V-STM

Agency

RoHS 2011/65/EU

Classification

Compliant

