

# BK4VXM-LCP-LCP



ProPatch® Mini LCP High-Performance Patch Cords, 4 ft

## Product Classification

<b>Brand</b>	Pro Patch®
<b>Product Series</b>	ProPatch
<b>Product Type</b>	RF cable assembly
<b>Regional Availability</b>	EMEA   Latin America   North America

## Dimensions

<b>Cord Length</b>	1.22 m   4.00 ft
--------------------	------------------

## Electrical Specifications

<b>Data Rate, Supported</b>	Uncompressed HDTV signals (1.485 Gbit/s)
<b>Impedance</b>	75 ohm
<b>Safety Voltage Rating</b>	600 V

## Environmental Specifications

<b>Environmental Space</b>	Indoor
<b>Operating Temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)

## General Specifications

<b>Cable Type</b>	240 Series
<b>Interface, connector A</b>	LCC plug
<b>Interface, connector B</b>	LCC plug
<b>Jacket Color</b>	Black
<b>Application</b>	For use with LCC video panels
<b>Interface Feature, connector A</b>	Booted
<b>Interface Feature, connector B</b>	Booted

## Mechanical Specifications

<b>Conductor Material</b>	Beryllium copper
<b>Contact Plating Material</b>	Gold

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

