

BK3VXM-LCP-LCP



ProPatch® Mini LCP High-Performance Patch Cords, 3 ft

Product Classification

| | |
|------------------------------|--------------------------------------|
| Brand | Pro Patch® |
| Product Series | ProPatch |
| Product Type | RF cable assembly |
| Regional Availability | EMEA Latin America North America |

Dimensions

| | |
|--------------------|------------------|
| Cord Length | 0.91 m 3.00 ft |
|--------------------|------------------|

Electrical Specifications

| | |
|------------------------------|--|
| Data Rate, Supported | Uncompressed HDTV signals (1.485 Gbit/s) |
| Impedance | 75 ohm |
| Safety Voltage Rating | 600 V |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Environmental Space | Indoor |
| Operating Temperature | -40 °C to +65 °C (-40 °F to +149 °F) |

General Specifications

| | |
|---------------------------------------|-------------------------------|
| Cable Type | 240 Series |
| Interface, connector A | LCC plug |
| Interface, connector B | LCC plug |
| Jacket Color | Black |
| Application | For use with LCC video panels |
| Interface Feature, connector A | Booted |
| Interface Feature, connector B | Booted |

Mechanical Specifications

| | |
|---------------------------------|------------------|
| Conductor Material | Beryllium copper |
| Contact Plating Material | Gold |

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

