



RJ45 Patch Cord, category 5e, PVC stranded, with security key, gray, 1 m

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair patch cord
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA

## Dimensions

<b>Cord Length</b>	1.00 m   3.28 ft
<b>Diameter Over Jacket</b>	4.90 mm   0.19 in

## Electrical Specifications

<b>ANSI/TIA Category</b>	5e
--------------------------	----

## Environmental Specifications

<b>Environmental Space</b>	Non-plenum
<b>Flammability Rating</b>	CM
<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)

## General Specifications

<b>Cable Type</b>	U/UTP (unshielded)
<b>Interface, connector A</b>	RJ45 plug with security key
<b>Interface, connector B</b>	RJ45 plug with security key
<b>Jacket Color</b>	Gray
<b>Pairs, quantity</b>	4

## Mechanical Specifications

<b>Conductor Type</b>	Stranded
<b>Conductor Gauge, stranded</b>	24 AWG
<b>Conductor Material</b>	Bare copper

## Regulatory Compliance/Certifications

**Agency**

**Classification**

