



RJ45 Patch Cord, category 5e, PVC stranded, with security key, gray, 2 m

OBSOLETE

This product was discontinued on: December 31, 2018

Product Classification

| | |
|------------------------------|-------------------------------------|
| Portfolio | NETCONNECT® |
| Product Type | Twisted pair patch cord |
| Regional Availability | Asia Australia/New Zealand EMEA |

Dimensions

| | |
|-----------------------------|-------------------|
| Cord Length | 2.00 m 6.56 ft |
| Diameter Over Jacket | 4.90 mm 0.19 in |

Electrical Specifications

| | |
|--------------------------|----|
| ANSI/TIA Category | 5e |
|--------------------------|----|

Environmental Specifications

| | |
|------------------------------|-------------------------------------|
| Environmental Space | Non-plenum |
| Flammability Rating | CM |
| Operating Temperature | -20 °C to +60 °C (-4 °F to +140 °F) |

General Specifications

| | |
|-------------------------------|-----------------------------|
| Cable Type | U/UTP (unshielded) |
| Interface, connector A | RJ45 plug with security key |
| Interface, connector B | RJ45 plug with security key |
| Jacket Color | Gray |
| Pairs, quantity | 4 |

Mechanical Specifications

| | |
|----------------------------------|----------|
| Conductor Type | Stranded |
| Conductor Gauge, stranded | 24 AWG |

1939121-2

Conductor Material Bare copper

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

