



MRJ21™ High Speed Cable Assembly, MRJ21-MRJ21, 180°-45°, 10GbE, 24-pair, S/U/FTP, 25 m

- Universal modular copper cabling platform for applications such as Gigabit Ethernet, VoIP and Power over Ethernet
- Increased I/O port density and cleaner cabling schemes compared to RJ45 connectors and cabling
- Robust die cast cable covers provide straight, or 45 deg left/right cable exit for ease of routing

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Brand</b>	MRJ21™
<b>Product Series</b>	MRJ21
<b>Product Type</b>	Copper trunk cable assembly
<b>Regional Availability</b>	EMEA

## Dimensions

<b>Cord Length</b>	25.00 m   82.02 ft
<b>Diameter Over Jacket</b>	11.50 mm   0.45 in

## Electrical Specifications

<b>ANSI/TIA Category</b>	6A
<b>Safety Voltage Rating</b>	150 V

## Environmental Specifications

<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
<b>Safety Standard</b>	cUL

## General Specifications

<b>Construction Type</b>	Stranded
<b>Interface, connector A</b>	MRJ21 plug
<b>Interface, connector B</b>	MRJ21 plug
<b>Application</b>	Ethernet, 10 GbE
<b>Cable Type</b>	S/FTP (shielded)
<b>Interface Feature, connector A</b>	Backshell, 180°
<b>Interface Feature, connector B</b>	Backshell, 45°
<b>Jacket Color</b>	White
<b>Package Quantity</b>	1
<b>Pairs, quantity</b>	24
<b>Total Ports, quantity</b>	6

## Mechanical Specifications

<b>Conductor Gauge, solid</b>	26 AWG
<b>Conductor Material</b>	Bare copper
<b>Conductor Type</b>	Solid

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

