

Fiber Optic Pigtail, Multi-fiber, Singlemode, 4 fibers, LC/UPC to Stub, 3 m

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber pigtail, multi-fiber
<b>Regional Availability</b>	Latin America   North America

## Construction Materials

<b>Fiber Type</b>	OS2
<b>Total Fibers, quantity</b>	4
<b>Fiber Mode</b>	Singlemode
<b>Jacket Color</b>	Yellow

## Dimensions

<b>Cord Length</b>	3.00 m   9.84 ft
--------------------	------------------

## General Specifications

<b>Interface, connector A</b>	LC/UPC
<b>Interface, connector B</b>	Unterminated
<b>Color, boot A</b>	Blue
<b>Connector A, quantity</b>	4
<b>Connector B, quantity</b>	0
<b>Package Quantity</b>	1
<b>Color, connector A</b>	Blue

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

