



MPO Trunk Cable, singlemode, MPO to MPO, yellow, 11 m

Product Classification

| | |
|------------------------------|--------------------------------------|
| Portfolio | NETCONNECT® |
| Brand | MPOptimate® |
| Product Type | Fiber trunk cable assembly |
| Regional Availability | EMEA Latin America North America |

Construction Materials

| | |
|-------------------------------|------------|
| Fiber Type | OS2 |
| Total Fibers, quantity | 12 |
| Jacket Color | Yellow |
| Fiber Mode | Singlemode |

Dimensions

| | |
|-----------------------------|--------------------|
| Cord Length | 11.00 m 36.09 ft |
| Diameter Over Jacket | 6.40 mm 0.25 in |

Environmental Specifications

| | |
|----------------------------|-------------------------------|
| Environmental Space | Low Smoke Zero Halogen (LSZH) |
|----------------------------|-------------------------------|

General Specifications

| | |
|-------------------------------|-------------------|
| Interface, connector A | MPO-12/APC Female |
| Interface, connector B | MPO-12/APC Female |
| Color, connector A | Green |
| Color, connector B | Green |
| Color, boot A | Black |
| Color, boot B | Black |
| Connector A, quantity | 1 |
| Connector B, quantity | 1 |
| Package Quantity | 1 |
| Polarity | Pairs, straight |

Optical Performance

Insertion Loss, maximum, connector A 0.60 dB

Insertion Loss, maximum, connector B 0.60 dB

Return Loss, minimum, connector A 45.00 dB

Return Loss, minimum, connector B 45.00 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

