



MPO Trunk Cable, singlemode, MPO to MPO, yellow, 19 m

Product Classification

Portfolio	NETCONNECT®
Brand	MPOptimate®
Product Type	Fiber trunk cable assembly
Regional Availability	EMEA Latin America North America

Construction Materials

Fiber Type	OS2
Total Fibers, quantity	12
Jacket Color	Yellow
Fiber Mode	Singlemode

Dimensions

Cord Length	19.00 m 62.34 ft
Diameter Over Jacket	6.40 mm 0.25 in

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

General Specifications

Interface, connector A	MPO-12/APC Female
Interface, connector B	MPO-12/APC Female
Color, connector A	Green
Color, connector B	Green
Color, boot A	Black
Color, boot B	Black
Connector A, quantity	1
Connector B, quantity	1
Package Quantity	1
Polarity	Pairs, straight

Optical Performance

Insertion Loss, maximum, connector A 0.60 dB

Insertion Loss, maximum, connector B 0.60 dB

Return Loss, minimum, connector A 45.00 dB

Return Loss, minimum, connector B 45.00 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

