

MPO Trunk Cable, singlemode, MPO to MPO, yellow, 115 m

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Brand</b>	MPOptimate®
<b>Product Type</b>	Fiber trunk cable assembly
<b>Regional Availability</b>	EMEA   Latin America   North America

## Construction Materials

<b>Fiber Type</b>	OS2
<b>Total Fibers, quantity</b>	24
<b>Jacket Color</b>	Yellow
<b>Fiber Mode</b>	Singlemode

## Dimensions

<b>Cord Length</b>	115.00 m   377.30 ft
<b>Diameter Over Jacket</b>	8.00 mm   0.31 in

## Environmental Specifications

<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

## General Specifications

<b>Interface, connector A</b>	MPO-12/APC Female
<b>Interface, connector B</b>	MPO-12/APC Female
<b>Color, connector A</b>	Green
<b>Color, connector B</b>	Green
<b>Color, boot A</b>	Black
<b>Color, boot B</b>	Black
<b>Connector A, quantity</b>	2
<b>Connector B, quantity</b>	2
<b>Package Quantity</b>	1
<b>Polarity</b>	Pairs, straight

## Optical Performance

<b>Insertion Loss, maximum, connector A</b>	0.75 dB
<b>Insertion Loss, maximum, connector B</b>	0.75 dB
<b>Return Loss, minimum, connector A</b>	35.00 dB
<b>Return Loss, minimum, connector B</b>	35.00 dB

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant

