

Fiber Optic Patch Cord, Multi-fiber, Singlemode, 12 fibers, SC/UPC to SC/UPC, yellow, 14 m

## Product Classification

<b>Product Series</b>	FPM
<b>Product Type</b>	Fiber distribution cable assembly
<b>Regional Availability</b>	Latin America   North America

## Construction Materials

<b>Fiber Type</b>	OS2
<b>Total Fibers, quantity</b>	12
<b>Fiber Mode</b>	Singlemode
<b>Jacket Color</b>	Yellow

## Dimensions

<b>Cord Length</b>	14.00 m   45.93 ft
<b>Breakout Length, connector A</b>	990.60 mm   39.00 in
<b>Breakout Length, connector B</b>	635.00 mm   25.00 in

## Environmental Specifications

<b>Environmental Space</b>	Plenum
----------------------------	--------

## General Specifications

<b>Interface, connector A</b>	SC/UPC
<b>Interface, connector B</b>	SC/UPC
<b>Color, boot A</b>	Blue
<b>Color, boot B</b>	Blue
<b>Color, connector A</b>	Blue
<b>Color, connector B</b>	Blue
<b>Connector A, quantity</b>	12
<b>Connector B, quantity</b>	12
<b>Construction Type</b>	Stranded
<b>Package Quantity</b>	1

## Optical Performance

<b>Insertion Loss, maximum, connector A</b>	0.20 dB
<b>Insertion Loss, maximum, connector B</b>	0.20 dB
<b>Return Loss, minimum, connector A</b>	57.00 dB
<b>Return Loss, minimum, connector B</b>	57.00 dB

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

