

Fiber Optic Patch Cord, Multi-fiber, Singlemode, 12 fibers, SC/UPC to SC/UPC, 42 m

Product Classification

Product Series	FPM
Product Type	Fiber distribution cable assembly
Regional Availability	Latin America North America

Construction Materials

Fiber Type	OS2
Total Fibers, quantity	12
Fiber Mode	Singlemode
Jacket Color	Yellow

Dimensions

Cord Length	42.00 m 137.80 ft
Breakout Length, connector A	990.60 mm 39.00 in
Breakout Length, connector B	635.00 mm 25.00 in

Environmental Specifications

Environmental Space	Plenum
----------------------------	--------

General Specifications

Interface, connector A	SC/UPC
Interface, connector B	SC/UPC
Color, boot A	Blue
Color, boot B	Blue
Color, connector A	Blue
Color, connector B	Blue
Connector A, quantity	12
Connector B, quantity	12
Construction Type	Stranded
Package Quantity	1

Optical Performance

Insertion Loss, maximum, connector A	0.20 dB
Insertion Loss, maximum, connector B	0.20 dB
Return Loss, minimum, connector A	57.00 dB
Return Loss, minimum, connector B	57.00 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

