

Fiber Optic Patch Cord, Multi-fiber, Singlemode, 4 fibers, LC/UPC to LC/UPC, yellow, 19 m

Product Classification

Product Series	FPM
Product Type	Fiber distribution cable assembly
Regional Availability	Latin America North America

Construction Materials

Fiber Type	OS2
Total Fibers, quantity	4
Fiber Mode	Singlemode
Jacket Color	Yellow

Dimensions

Cord Length	19.00 m 62.34 ft
--------------------	--------------------

Environmental Specifications

Environmental Space	Plenum
----------------------------	--------

General Specifications

Interface, connector A	LC/UPC
Interface, connector B	SC/UPC
Color, boot A	Blue
Color, boot B	Blue
Color, connector A	Blue
Color, connector B	Blue
Connector A, quantity	4
Connector B, quantity	4
Construction Type	Stranded
Package Quantity	1

Optical Performance

Insertion Loss, maximum, connector A	0.30 dB
Insertion Loss, maximum, connector B	0.20 dB
Return Loss, minimum, connector A	55.00 dB
Return Loss, minimum, connector B	55.00 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

