

Fiber Optic Pigtail, Multi-fiber, Singlemode, 12 fibers, SC/APC to Stub, white, 10 m

## Product Classification

<b>Product Series</b>	RICO
<b>Product Type</b>	Fiber pigtail, multi-fiber
<b>Regional Availability</b>	EMEA

## Construction Materials

<b>Fiber Type</b>	G.657.A1
<b>Total Fibers, quantity</b>	12
<b>Fiber Mode</b>	Singlemode
<b>Jacket Color</b>	White

## Dimensions

<b>Cord Length</b>	10.00 m   32.81 ft
--------------------	--------------------

## Environmental Specifications

<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

## General Specifications

<b>Construction Type</b>	Stranded
<b>Interface, connector A</b>	SC/APC
<b>Interface, connector B</b>	Unterminated
<b>Color, boot A</b>	Green
<b>Connector A, quantity</b>	12
<b>Connector B, quantity</b>	0
<b>Package Quantity</b>	1
<b>Color, connector A</b>	Green

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

