

LS2-HMHM-X



LSF2 SureFlex® Jumper Kit with interface types 4.3-10 Male and 4.3-10 Male, variable lengths, (connector A - the factory-attached end, and connector B - the field-fit/bagged end) Field-fit connector not for individual sale - only available as part of the LS2 assembly.

- **WARNING: DO NOT MATE WITH 4.1-9.5 DIN**

Logo Image

Product Classification

Product Series	LSF2-50
Product Type	Wireless transmission cable assembly

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Nominal Size	3/8 in
Attachment, Connector A	Factory attached
Attachment, Connector B	Field attachment
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Electrical Specifications

3rd Order IMD Dynamic	-159.00 dBc -116.00 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037

Environmental Specifications

Immersion Test Method	Meets IEC 60529:2001, IP68 in mated condition
------------------------------	---

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–970 MHz	1.08	28.00
1700–2200 MHz	1.08	28.00
2200–2700 MHz	1.11	26.00
3400–3800 MHz	1.13	24.00
4000–6000 MHz	1.22	20.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)

