



RJ45 Patch Cord, category 6, U/UTP, with security key, white, 10 m

- Both ends have a security key plug mechanism
- Prevents unauthorized disconnection
- Can be used for secure connections (e.g. server lines)

Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA

Dimensions

Cord Length	10.00 m 32.81 ft
Diameter Over Jacket	5.58 mm 0.22 in

Electrical Specifications

ANSI/TIA Category	6
--------------------------	---

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
------------------------------	-------------------------------------

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug with security key
Interface, connector B	RJ45 plug with security key
Jacket Color	White
Includes	Security key (2)
Package Quantity	1
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Stranded
Conductor Gauge, stranded	24 AWG

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------



Included Products

1871456-2 — RJ45 Security Key Plug kit with reserved number

RJ45 Security Key Plug kit with reserved number



Product Classification

Portfolio	NETCONNECT®
Product Type	Security key kit
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

General Specifications

Color	Ivory
Package Quantity	1
Packaging Type	Box Carton

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

