

LS2-HMHM-2-D



D-CLASS LSF2-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, 2 ft

- **WARNING: DO NOT MATE WITH 4.1-9.5 DIN**

Logo Image

Product Classification

Product Series	LSF2-50
Product Type	Wireless transmission cable assembly

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Length	0.610 m 2.000 ft
Nominal Size	3/8 in
Specification Sheet Revision Level	A

Electrical Specifications

3rd Order IMD Dynamic	-162.00 dBc -119.00 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037

Environmental Specifications

Immersion Test Method	Meets IEC 60529:2001, IP68 in mated condition
------------------------------	---

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.07	30.00
1700–2200 MHz	1.07	30.00
2200–2700 MHz	1.08	28.00
3400–3800 MHz	1.11	26.00
4000–6000 MHz	1.17	22.00

Antenna Input Dimensions

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant by Exemption

Designed, manufactured and/or distributed under this quality management system

Above Maximum Concentration Value (MCV)

