



AMPINNERGY® Power-to-Line Cable Assembly, 8-wire/3-circuit (3-1-1), shared neutral, 50 feet

- Used to jumper system components together and can be used to extend power-to-power cable assemblies
- Mates with power connector and line connector cable assemblies, power junction boxes, power distribution modules, zone distribution modules, and power transition units

Product Classification

| | |
|------------------------------|------------------------------|
| Brand | AMPINNERGY® |
| Product Series | AMPINNERGY |
| Product Type | Power-to-line cable assembly |
| Regional Availability | North America |

Dimensions

| | |
|--------------------|--------------------|
| Cord Length | 15.24 m 50.00 ft |
|--------------------|--------------------|

Electrical Specifications

| | |
|--------------------------------|-------------------------|
| Current Rating, maximum | 20.00 A |
| Voltage Rating, maximum | 125.00 Vac 250.00 Vac |

Environmental Specifications

| | |
|----------------------------|--|
| Environmental Space | Indoor |
| Safety Standard | CEC 2015 CSA 22.2 NEC 2013 UL 1286 UL 183 UL 498 |

General Specifications

| | |
|---------------------------------------|--------------------------|
| Application | Power to line connection |
| Construction Type | Corrugated hose |
| Interface, connector A | Power male plug |
| Interface, connector B | Line female plug |
| Neutral Conductor Gauge, solid | 10 AWG |
| Neutral Type | Shared |
| Package Quantity | 1 |
| Packaging Type | Bag |

Mechanical Specifications

| | |
|---------------|--------------------------|
| Wiring | 5-Wire/3 Circuit (3-1-1) |
|---------------|--------------------------|

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

