



MPO Fanout Cable, Multimode, 12 fibers, MPO to LC/UPC, aqua, 10 m

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber fanout cable assembly
<b>Regional Availability</b>	EMEA   Latin America   North America

## Construction Materials

<b>Fiber Type</b>	OM3
<b>Total Fibers, quantity</b>	12
<b>Jacket Color</b>	Aqua
<b>Fiber Mode</b>	Multimode

## Dimensions

<b>Cord Length</b>	10.00 m   32.81 ft
--------------------	--------------------

## Environmental Specifications

<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

## General Specifications

<b>Construction Type</b>	Plug-and-play, array cord
<b>Interface, connector A</b>	MPO-12/UPC Female
<b>Interface, connector B</b>	LC/UPC
<b>Color, connector A</b>	Aqua
<b>Color, connector B</b>	Beige
<b>Color, boot A</b>	Black
<b>Color, boot B</b>	Beige
<b>Connector A, quantity</b>	1
<b>Connector B, quantity</b>	12
<b>Package Quantity</b>	1

## Optical Performance

<b>Insertion Loss, maximum, connector A</b>	0.35 dB
---	---------

# 1-1859490-0

---

**Insertion Loss, maximum, connector B** 0.15 dB  
**Return Loss, minimum, connector A** 28.00 dB  
**Return Loss, minimum, connector B** 35.00 dB

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

