



MPO Fanout Cable, OM3, MPO male to 12xLC/PC, 10 m

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber fanout cable assembly
Regional Availability	Australia/New Zealand EMEA

Construction Materials

Fiber Type	OM3
Total Fibers, quantity	12
Jacket Color	Aqua
Fiber Mode	Multimode

Dimensions

Cord Length	10.00 m 32.81 ft
Diameter Over Jacket	6.40 mm 0.25 in

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

General Specifications

Construction Type	Plug-and-play, array cord
Interface, connector A	MPO-12/UPC Male
Interface, connector B	LC/UPC
Color, connector A	Aqua
Color, connector B	Beige
Color, boot A	Black
Color, boot B	Beige
Connector A, quantity	1
Connector B, quantity	12
Package Quantity	1
Polarity	Pairs, straight

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

