

LazrSPEED® 300 SC to SC, InstaPATCH® 360 Ruggedized Fanout Cable, 36-Fiber, LSZH

## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	InstaPATCH® 360   LazrSPEED®
<b>Product Type</b>	Fiber fanout cable assembly
<b>Regional Availability</b>	EMEA

## Construction Materials

<b>Fiber Type</b>	OM3, LazrSPEED® 300
<b>Total Fibers, quantity</b>	36
<b>Fibers per Subunit, quantity</b>	12
<b>Furcation Color</b>	Aqua

## Dimensions

<b>Cord Length, maximum</b>	999 ft   999 m
<b>Cord Length, minimum</b>	3 m   8 ft
<b>Ordering Note</b>	For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration

## Environmental Specifications

<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)

## General Specifications

<b>Interface, connector A</b>	SC/UPC
<b>Interface, connector B</b>	SC/UPC
<b>Color, connector A</b>	Beige
<b>Color, connector B</b>	Beige
<b>Construction Type</b>	InstaPATCH® 360 ruggedized fanout, indoor
<b>Cord Configurator</b>	Yes
<b>Ordering Note</b>	Not available in the United States or Canada

## Mechanical Specifications

<b>Cable Retention Strength, maximum</b>	11.24 lb @ 0 °   4.40 lb @ 90 °
--	---------------------------------

## Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

RoHS 2011/65/EU  
ISO 9001:2015

Compliant  
Designed, manufactured and/or distributed under this quality management system



## Included Products

460125750 (Product Component—not orderable) — LazrSPEED® Pre-Radiused SC Connector for 1.6 mm Fiber Cordage, Duplex, multimode

760239594 | N-036-MP-5I-F12AQ/B2 (Product Component—not orderable) — LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk Cable, 12 fiber subunits

- CS-5L-MP (Product Component—not orderable) — LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber