

LazrSPEED® 550 SC to SC, InstaPATCH® 360 Ruggedized Fanout Cable, 72-Fiber, LSZH

Product Classification

Portfolio	SYSTIMAX®
Brand	InstaPATCH® 360 LazrSPEED®
Product Type	Fiber fanout cable assembly
Regional Availability	EMEA

Construction Materials

Fiber Type	OM4, LazrSPEED® 550
Total Fibers, quantity	72
Fibers per Subunit, quantity	12
Furcation Color	Aqua

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	3 m 8 ft
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Interface, connector A	SC/UPC
Interface, connector B	SC/UPC
Color, connector A	Beige
Color, connector B	Beige
Construction Type	InstaPATCH® 360 ruggedized fanout, indoor
Cord Configurator	Yes
Ordering Note	Not available in the United States or Canada

Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 ° 4.40 lb @ 90 °
--	---------------------------------

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

RoHS 2011/65/EU
ISO 9001:2015

Compliant
Designed, manufactured and/or distributed under this quality management system



Included Products

460125750 (Product Component—not orderable) — LazrSPEED® Pre-Radiused SC Connector for 1.6 mm Fiber Cordage, Duplex, multimode

760239602 | N-072-MP-5K-F12AQ/B2 (Product Component—not orderable) — LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk Cable, 12 fiber subunits

- CS-5K-MP (Product Component—not orderable) — LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber