

LS2-HMHM-5-D



D-CLASS LSF2-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, 5 ft

- **WARNING: DO NOT MATE WITH 4.1-9.5 DIN**

Logo Image

Product Classification

Product Series	LSF2-50
Product Type	Wireless transmission cable assembly

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Length	1.524 m 5.000 ft
Nominal Size	3/8 in
Specification Sheet Revision Level	A


Electrical Specifications

3rd Order IMD Dynamic	-162.00 dBc -119.00 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037

Environmental Specifications

Immersion Test Method	Meets IEC 60529:2001, IP68 in mated condition
------------------------------	---

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.07	30.00
1700–2200 MHz	1.07	30.00
2200–2700 MHz	1.08	28.00
3400–3800 MHz	1.11	26.00
4000–6000 MHz	1.17	22.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)

