

1-1859919-0

RJ45 Patch Cord, category 6A, S/FTP, 30 AWG, stranded, LSZH, red, 10 m



Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA

Dimensions

Cord Length	10.00 m 32.81 ft
--------------------	--------------------

Electrical Specifications

ANSI/TIA Category	6A
Impedance	100 ohm

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

General Specifications

Cable Type	S/FTP (shielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Red
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Stranded
Conductor Gauge, stranded	30 AWG
Wiring	T568B

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

