

FHBDW-H2Q22-0250F



HELIAX® FiberFeed® Discrete: Single mode 2 fiber drop assembly, hardened SC/APC to LC Duplex, Ericsson 2203 / 2205, 250 ft

Product Classification

Portfolio	CommScope®
Brand	FiberFeed® HELIAX®
Product Series	FHBDW
Product Type	Wireless Fiber Cable Assemblies
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.657.A2
Total Fibers, quantity	2
Jacket Color	Black

Dimensions

Cord Length	76.20 m 250.00 ft
--------------------	---------------------

Environmental Specifications

Environmental Space	Outdoor
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Interface Body Style, connector A	Straight
Interface Body Style, connector B	Straight
Interface, connector A	SC/APC
Interface, connector B	DLC
Minimum Bend Radius, furcation	61.0 mm 2.4 in
Ordering Note	CommScope® non-standard product

Optical Performance

Assembly Insertion Loss, typical	0.75 dB
Assembly Insertion Loss, typical note	Insertion loss is measured at 1310 and 1550 nm

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Assembly Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)