


SRS-STHT-SLNU-OR-G



SpeedPRO™ Straight Slotted Channel with hinged cover, 100 mm x 50 mm (4 in x 2 in), 2 m (6 ft 6 in) length, orange

Product Classification

Portfolio	CommScope®
Brand	SpeedPRO™
Product Type	Fiber raceway channel, with hinged cover
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

System Dimensions	100 mm x 50 mm 4 in x 2 in
Length	2000.0 mm 78.7 in
Weight	2.41 kg 5.31 lb

Environmental Specifications

Flammability Rating	UL 94 V-0
Halogen Characteristics	LSZH
Safety Standard	UL

General Specifications

Color	Orange
Minimum Order Quantity	1
Package Quantity	1
Section Type	Straight section
Warranty	20 years

Mechanical Specifications

Material Type	PPO/PS
----------------------	--------