

F4WMPSCAK

TeraSPEED® MPO (female) to SC, InstaPATCH® 360 Ruggedized Fanout Cable, 72-Fiber, LSZH

Product Classification

Portfolio	SYSTIMAX®
Brand	InstaPATCH® 360 TeraSPEED®
Product Type	Fiber fanout cable assembly
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	72
Fibers per Subunit, quantity	12
Furcation Color	Yellow

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	3 m 8 ft
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Construction Type	InstaPATCH® 360 ruggedized fanout, indoor
Interface, connector A	MPO-12/APC Female
Interface, connector B	SC/UPC
Color, connector A	Green
Color, connector B	Blue
Ordering Note	Not available in the United States or Canada

Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
--	----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

F4WMPSCAK

RoHS 2011/65/EU
ISO 9001:2015

Compliant
Designed, manufactured and/or distributed under this quality management system



Included Products

860366137 (Product Component—not orderable) — TeraSPEED® MPO Female 12 Fiber Connector, green

460125768 (Product Component—not orderable) — TeraSPEED® Pre-Radiused SC Connector for 1.6 mm Fiber Cordage, Duplex, single-mode

760239615 | N-072-MP-8W-F12YL/B2 (Product Component—not orderable) — TeraSPEED® Low Smoke Zero Halogen Riser MPO Trunk Cable, 12 fiber subunits

- CS-8W-MP (Product Component—not orderable) — TeraSPEED® OS2 Singlemode Fiber