



ION®-E Wireless Communications Switch Subrack, 4 U

OBSOLETE**Replaced By**7635442-01
WCS-4

ION®-E Wireless Communications Switch Subrack, 4 U

Product Classification

Brand	Era™ ION®-E
Product Type	Subrack

General Specifications

Includes	Fan filter Fan tray
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Rack Type	EIA 19 in

Electrical Specifications

Electrical Safety Standard	EN 60950
Power Consumption	70 W
Voltage Range	12 Vdc

Mechanical Specifications

Mounting	Rack
Slots Available, quantity	19

Environmental Specifications

Mean Time Between Failures (MTBF)	33 yr @ 25 °C
Operating Temperature	+5 °C to +40 °C (+41 °F to +104 °F)

Dimensions

Depth	450.00 mm 17.72 in
Height	177.00 mm 6.97 in
Net Weight	10.80 kg 23.81 lb

Width 482.00 mm | 18.98 in

Packed Dimensions

Depth 185.0 mm | 7.3 in

Height 522.0 mm | 20.6 in

Width 585.0 mm | 23.0 in