

Fiber Optic Cable, 24-fiber, OM4, 1000 m, aqua

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber indoor/outdoor cable
Regional Availability	Asia Australia/New Zealand EMEA

Standards And Qualifications

EN50575 CPR Cable EuroClass	Eca
------------------------------------	-----

Optical Specifications, Wavelength Specific

Attenuation, maximum	1.00 dB/km @ 1300 nm 3.50 dB/km @ 850 nm
Standards Compliance	IEC 60794-1 TIA-492AAAD (OM4)

General Specifications

Cable Type	Loose tube
Subunit Type	Gel-free

Construction Materials

Total Fiber Count	24
Fiber Type	OM4
Fibers per Subunit, quantity	12
Jacket Color	Aqua

Dimensions

Cable Length	1000 m 3281 ft
Cable Weight	119.0 kg/km
Diameter Over Jacket	11.50 mm 0.45 in
Filler, quantity	2

Physical Specifications

Minimum Bend Radius, loaded	229.9 mm 9.1 in
Minimum Bend Radius, unloaded	169.9 mm 6.7 in
Tensile Load, long term, maximum	1201 N 270 lbf
Tensile Load, short term, maximum	2002 N 450 lbf

Environmental Specifications

Environmental Space	Universal Low Smoke Zero Halogen (ULSZH)
Installation Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Operating Temperature	-10 °C to +70 °C (+14 °F to +158 °F)
Storage Temperature	-10 °C to +70 °C (+14 °F to +158 °F)

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable