



640 Series Copper Cable, category 6A, 4 pair, FTP, 23 AWG, 305 m, blue

OBSOLETE

This product was discontinued on: **March 18, 2019**

Replaced By

884032108/10 CS44CM BLU C6A 4/23 F/UTP RL 305M (APAC/EMEA/NAR)	CS44CM Category 6A, F/UTP Cable, non-plenum, blue jacket, 4 pair count, 1000 ft (305 m) length reel
884025308/10 CS44CM BLU C6A 4/23 F/UTP RL 305M (CALA)	CS44CM Category 6A, F/UTP Cable, non-plenum, blue jacket, 4 pair count, 1000 ft (305 m) length reel, ANATEL

Product Classification

Portfolio	NETCONNECT®
Product Series	640 Series
Product Type	Twisted pair cable
Regional Availability	Asia Latin America

Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Insulation Material	Polyolefin
Shield (Tape) Material	Aluminum/Polyester

Dimensions

Cable Length	305 m 1000 ft
Diameter Over Jacket, nominal	7.200 mm 0.283 in

Electrical Specifications

ANSI/TIA Category	6A
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-6-1 ISO/IEC 11801 Class E

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
------------------------------	-------------------------------------

General Specifications

Cable Type	F/UTP (shielded)
Packaging Type	Reel
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	Blue
Product Number	620M
Conductor Gauge, singles	23 AWG
Conductor Type, singles	Solid
Conductors, quantity	8

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

