

Outdoor Fiber Cable, 12-fiber, singlemode OS2, loose tube s/sheath, black

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber OSP cable
Regional Availability	Australia/New Zealand

Optical Specifications, Wavelength Specific

Standards Compliance	TIA-492CAAB (OS2)
-----------------------------	-------------------

General Specifications

Cable Type	Loose tube
Subunit Type	Gel-filled

Construction Materials

Jacket Material	Nylon
Total Fiber Count	12
Fiber Type	OS2
Fibers per Subunit, quantity	12
Jacket Color	Black

Dimensions

Diameter Over Jacket	10.90 mm 0.43 in
-----------------------------	--------------------

Environmental Specifications

Environmental Space	Buried
Operating Temperature	-10 °C to +70 °C (+14 °F to +158 °F)

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable