



Undercarpet Copper Cable, category 6, 4-pair, 8 conductors, unshielded, 100 ft, white

- Exceeds TIA/EIA and ISO specifications for Categories specified
- Exceeds all requirements for Gigabit Ethernet
- Leadfree jacketing

Product Classification

Portfolio	NETCONNECT®
Product Series	Undercarpet
Product Type	Twisted pair cable
Regional Availability	North America

Construction Materials

Conductor Material	Bare copper
---------------------------	-------------

Dimensions

Cable Length	30 m 100 ft
---------------------	---------------

Electrical Specifications

ANSI/TIA Category	6
Operating Voltage, maximum	80 V
Safety Voltage Rating	300 Vac

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Cable Type	U/UTP (unshielded)
Pairs, quantity	4
Supported Application	Commercial Office Retail
Jacket Color	White
Conductor Gauge, singles	24 AWG

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

