



510 Series Copper Cable, category 5e, 4 pair, U/UTP, 24 AWG, PVC, 200 m, white

Product Classification

Portfolio	NETCONNECT®
Product Series	510 Series
Product Type	Twisted pair cable
Regional Availability	Asia

Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Insulation Material	Polyolefin

Dimensions

Cable Length	200 m 656 ft
Diameter Over Jacket, nominal	4.800 mm 0.189 in

Electrical Specifications

ANSI/TIA Category	5e
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-6-1 ISO/IEC 11801 Class D

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
------------------------------	-------------------------------------

General Specifications

Cable Type	U/UTP (unshielded)
Packaging Type	Reelex
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	White
Product Number	510H
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid

Conductors, quantity 8

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

