



Copper Cable, category 6, 4 pair, U/UTP, 24 AWG, 1000 ft reel-in-box, gray

Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair cable
Regional Availability	Asia

Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Insulation Material	Polyolefin

Dimensions

Cable Length	305 m 1000 ft
Diameter Over Jacket, nominal	5.600 mm 0.220 in

Electrical Specifications

ANSI/TIA Category	6
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-6-1 ISO/IEC 11801 Class E

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
------------------------------	-------------------------------------

General Specifications

Cable Type	U/UTP (unshielded)
Packaging Type	Reel in box
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	Gray
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid
Conductors, quantity	8

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

