

Indoor/outdoor Fiber Optic Cable, 4-fiber, OS2, yellow

OBSOLETE

This product was discontinued on: June 13, 2018

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber indoor/outdoor cable
Regional Availability	Asia Australia/New Zealand EMEA

Standards And Qualifications

EN50575 CPR Cable EuroClass Cca | s1 | d0 | a2

Optical Specifications, Wavelength Specific

Attenuation, maximum (temporary)	0.25 dB/km @ 1,300 nm
Standards Compliance	IEC 60794-1 TIA-492CAAB (OS2)

General Specifications

Cable Type Tight buffer

Construction Materials

Total Fiber Count	4
Fiber Type	OS2
Fibers per Subunit, quantity	4
Jacket Color	Yellow

Dimensions

Cable Length	2000 m 6562 ft
Cable Weight	27.0 kg/km
Diameter Over Jacket	5.00 mm 0.20 in

Physical Specifications

Minimum Bend Radius, loaded	75.0 mm 3.0 in
Minimum Bend Radius, unloaded	50.0 mm 2.0 in
Tensile Load, long term, maximum	350 N 79 lbf
Tensile Load, short term, maximum	650 N 146 lbf

Environmental Specifications

Environmental Space	Universal Low Smoke Zero Halogen (ULSZH)
Installation Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-20 °C to +70 °C (-4 °F to +158 °F)

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable