



640 Series Copper Cable, category 6A, 4 pair, UTP, CMR rated, 1000 ft, gray

OBSOLETE

This product was discontinued on: November 1, 2017

Replaced By

884019304/10 CS44R ETL Verified Category 6A U/UTP Cable, non-plenum, gray jacket, 4 pair count, 1000 ft (305 m) length, reel
CS44R GRY C6A 4/23 U/UTP RL 1 KFT

Product Classification

Portfolio	NETCONNECT®
Product Series	640 Series
Product Type	Twisted pair cable
Regional Availability	Asia Australia/New Zealand Latin America North America

Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Insulation Material	Polyolefin

Dimensions

Cable Length	305 m 1000 ft
Cable Weight	39.00 lb/kft
Diameter Over Jacket, nominal	7.570 mm 0.298 in

Electrical Specifications

ANSI/TIA Category	6A
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-6-1 ISO/IEC 11801 Class E

Environmental Specifications

Environmental Space	Non-plenum
Operating Temperature	-20 °C to +75 °C (-4 °F to +167 °F)

General Specifications

Cable Type	U/UTP (unshielded)
Packaging Type	Reel
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	Gray
Product Number	640R
Conductor Gauge, singles	23 AWG
Conductor Type, singles	Solid
Conductors, quantity	8

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

