



Undercarpet Copper Cable, category 5e, 4-pair, 8 conductors, unshielded, 100 ft, gray

- Exceeds TIA/EIA and ISO specifications for Categories specified
- Exceeds all requirements for Gigabit Ethernet
- Leadfree jacketing

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Series</b>	Undercarpet
<b>Product Type</b>	Twisted pair cable
<b>Regional Availability</b>	North America

## Construction Materials

<b>Conductor Material</b>	Bare copper
---------------------------	-------------

## Dimensions

<b>Cable Length</b>	30 m   100 ft
---------------------	---------------

## Electrical Specifications

<b>ANSI/TIA Category</b>	5e
<b>Operating Voltage, maximum</b>	80 V
<b>Safety Voltage Rating</b>	300 Vac

## Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

## General Specifications

<b>Cable Type</b>	U/UTP (unshielded)
<b>Pairs, quantity</b>	4
<b>Supported Application</b>	Commercial Office   Retail
<b>Jacket Color</b>	Gray
<b>Conductor Gauge, singles</b>	24 AWG

## Regulatory Compliance/Certifications

<b>Agency</b>	RoHS 2011/65/EU
---------------	-----------------

<b>Classification</b>	Compliant
-----------------------	-----------

